



ADELPHI MANUFACTURING

Increase efficiency and productivity with the Response Benchtop Filling Machine, for the **Pharmaceutical, Cosmetics, Food & Chemical** Industries



Proven concept, over 600 units supplied to 19 countries

High quality, appreciated by the most demanding customers, including Unilever, GSK, Novartis, Reckitt Benckiser, as well as Universities, NHS Hospitals and more.

Reduces product waste, increases profitability

- Exceptional filling accuracy of up to $\pm 0.25\%$ significantly improves your ROI.
- Manual filling gives an average accuracy of $\pm 10\%$ - overfilling just ten vials could mean giving away one full measure of product for free! We can prevent this for you - in 1,000 units, you may give away as much as 100 containers full of your product free of charge!

Time-efficient, fast filling

- An average of 20 - 40 containers per minute; choose the ideal filling speed to best suit your product.
- One customer has increased production from 30 containers per day being filled manually, to 400 being filled in one run by the Response! From just 600 containers per month, this translates into a phenomenal 64,000 containers!



[Watch a video of the Response filler >>>](#)

[Download the Response Brochure >>>](#)



ADELPHI MANUFACTURING

Space-efficient

- Small footprint - 340 x 840 x 343mm, to conveniently fit on a small table.
- Filling an equal number of containers manually would take up to 3 colleagues, which makes the same production space up to 2/3 less profitable!

Exceptionally hygienic

- 316L pharmaceutical grade stainless steel wetted parts adhere to FDA regulations, to guarantee international pharma-quality compliance for your business.
- Reduce the contamination risks to your product by reducing manual processes, so it comes into contact with fewer people.

Increase production; semi to fully automatic, for a fraction of the cost

- The Response Benchtop Filler can be incorporated into Adelphi's Response Monobloc Filler and Capper, or up to four Benchtop Fillers can be incorporated into the fully automated Response Automation line – this means that the initial investment is never obsolete.



Our technical team will be delighted to suggest the best specification for you. Please share with us the below information, so that we can prepare a quotation:

1. Product Details
2. Product Viscosity
3. The container volumes required to be filled
4. The filling speeds expected

[Contact our Sales Team for a quotation >>>](#)